


TTH machine

The TTH machine is used to evaluate the behaviour of pellets under specific conditions according to ISO 3271.

The machine is designed according to ISO 3271 to meet the demands of performance and functionality and is also encapsulated. It is designed to be installed in a tough environment.

Pneumatic opening and closing. Gear motor and separate break.

The machine is delivered complete with control system or an external override system and is also CE-certified.



Description	Data
Drum - inner diameter	1000 (mm)
Drum - inner length	570 (mm)
Dimensions (W x H x D)	1500 x 2200 x 1600
Weight	600 (kg)
Gearmotor (capacity)	2,2 (kW)